

Technical Data Sheet

General

Article number: 8600

Description: Colad Advanced Cut



Specification

A solvent- and silicone-free cutting compound for quick and aggressive polishing. Solvent-free and therefore user friendly / not affecting plastic parts and rubber seals, can be used on all kind of surfaces and makes additional masking unnecessary. Doesn't dry out as quick as solvent based compounds.

Can be used directly after sanding with P1200 or P1500.

The best result is achieved by using a Colad Clean Pad Hard and rotary machine.

For an improved and high gloss finish follow up with Colad OneStepReady.

Content: 1 kg

Master carton: 12 bottles

Remarks

Terms of use:

Shake well before use. Make sure the surface is clean before applying Colad Advanced Cut. Apply sufficient amount of Advanced Cut on to the polishing pad and distribute evenly. Start polishing with medium pressure on the machine (medium-high speed, 1300-1500 RPM). Reduce pressure when the polishing material starts to dry till all scratches are disappeared. Remove leftover compound with Hamach Microfiber Cloth [Art.no. 000812]. For an improved finish follow up with Colad OneStepReady [Art.no. 8700].

Store:

Above 10 °C, don't expose to frost or direct sunlight.

Shelf life - 24 months.

EUH 210: Material Safety Data Sheet available on request.

Created by :

E.M.M. International BV

Marsweg 59

8013 PE Zwolle

The Netherlands

phone +31 38 4676600

fax +31 38 4676699

www.emm.com